


INSTALLATION REQUIREMENTS

- (E) Single 208V/240V, 1- or 3-Phase; or optional 480V, 3-phase electrical connection

- Installation under approved vent hood may be required. Consult local codes. [Power connection from rear. See below]

OPTIONS & ACCESSORIES

- ☐ 480 Volt, 3-phase model [no charge]
- ☐ 8' Power Cord Kit with NEMA L15-30P plug
- ☐ 4" legs with adjustable bullet feet
- ☐ 28" stainless steel tubular leg stand with bullet feet
- ☐ 28" stainless steel tubular leg stands with pan slides & bullet feet
- ☐ 28" stainless steel tubular leg stands with casters
- ☐ 28" stainless steel tubular leg stands with pan slides & casters
- ☐ 16" stainless steel tubular leg stand with bullet feet for stacked EHS units
- ☐ 16" stainless steel tubular leg stands with casters for stacked EHS units
- ☐ Factory installed modem [Platinum/-PT models only]
- ☐ Factory recipe programming [Purple Plus/-PP & Platinum/-PT models only]
- ☐ Reversible door [hinged left or right]
- ☐ Extra wire pan racks [5 provided as std.]



Model	Height x Width x Depth (without optional stand)	Clearance from combustible surface	Weight		Freight Class
			Actual	Shipping	
EHS	25.3" x 30.2" x 25.3" 642mm x 766mm x 643mm	Sides: 6" (153mm) Back: 6" (153mm) Floor: 6" (153mm)	185 lbs. 84 kg	225 lbs. 102 kg	85

Model	(E) Electrical Requirements			
	Voltage	Total kW	Phase	Amps/Line
EHS	208V/60Hz	7.8	1	37.5
	240V/60Hz	7.8	1	32.5
	208V/60Hz	7.8	3	22.1
	240V/60Hz	7.8	3	19.1
	480V/60Hz	7.8	3	9.6

CAD SYMBOLS & PRICING



Due to continuous improvements, specifications subject to change without notice.



Sheet No. LSP-C9 (rev. 7/03)